



Please also note our general details and sales information

Edition 22.08.2024

Errors and amendments excepted. Our General Terms and Conditions are effective. / WEEE-Reg.-No. DE 69718127

INNOVATION		SEAT ADJUSTMENT		HEAD PICE ADJUSTMENT	COMFORT FUNCTIONS		
<ul style="list-style-type: none"> ● standard equipment □ extra equipment ■ extra equipment motor-driven adjustment only with mains operation 		motor-driven: back and leg part separate	with rechargeable battery without mains cable	manual	LIFT-up stand up assistance	massage	following on armrest
V2	in S I M I L	VS2	VM2	VL2	●	□	●
V4	in S I M I L	VS4	VM4	VL4	●	□	●

DESIGN

CONSTRUCTIVE DESIGN

All the materials used correspond to the requirements according to RAL-GZ 430/4.

Functional armchair, metal base frame

Seat upholstery structure: zig-zag springs, Dacron, pocket barrel spring, polystyrene foam VW 40, Diolen



Back upholstery structure: Dacron, polystyrene foam, Diolen

UPHOLSTERY CASUAL / LOOSE

With casual upholsteries you are rather sitting „in the sofa“ than on it, the upholstery snuggles. A casual/loose upholstery is characterized by a smooth upholstery structure. The cover is not waveless. The ridge of the covers on the seat, back and armrests as well as sitzmarks due to the model and design are typical.



BACK TENSIONING SECTIONS

All back tensioning sections are supplied as standard with the original cover.

SEAM

Depending on the model, the seam on leather covers may be different from fabric covers, especially on fitted items. Decorative leather seam (as felled seams or double seams) may be omitted depending on the model according to suitability of the fabric covering material.

The model is only worked with selvedge seam.

ERGONOMICS

In each version the armchair is available in the 3 sizes S, M, L. All relevant comfort sizes (seat height, seat depth, length of the leg flap, back height) are expanding in due proportion, adapted to all body measurements.



Constructive structure and elected materials ensure that the standards of the quality assessments and test instructions of RAL-GZ 430 are not only achieved but exceeded. Our products are designed for a max. static loading of 125 kg per seat.





Please also note our general details and sales information

Edition 22.08.2024

Errors and amendments excepted. Our General Terms and Conditions are effective.

FUNCTIONS

I FUNCTIONAL HEAD PIECE

The head piece can be adjusted by a ratchet mechanism that allows different positions. By pulling beyond the highest position the head piece can be returned to the basic position.

II FOLLOWING ON ARMREST

Ergonomic, following on armrests that adapt automatically optimal to the respective seat- or lying position.

III RELAX FUNCTION

Integrated seat adjustment: Back and leg part can be adjusted separate of each other for a comfortable relax position into a lying position.

MOTOR-DRIVEN RELAX FUNCTION

VS2, VM2, VL2

By operation of the sidewise fixed control panel (standing in front on the left) the back and the leg part can be adjusted infinitely separate of each other into a lying position.

The motor-driven relax function is actuated by mains current. It can also be delivered **with rechargeable battery** against extra charge.



MOTOR-DRIVEN RELAX FUNCTION WITH LIFT-UP FUNCTION

VS4, VM4, VL4

In addition to the motor-driven adjustment with this version a useful stand up assistance (LIFT-up function) is integrated. Instead of the control panel a cable hand switch is delivered with which all functions can be operated. The armchair is not rotatable in the moved out LIFT-up position.

Only with mains current (**rechargeable battery is not possible**).



Please note: Do not sit on the raised leg part. The joint is not designed for use with the entire weight of the body.



The leg part of the armchairs with LIFT-up (V4) has an angle of 30° compared to the motor-driven version (15°).

IV COMFORT PACKAGE MASSAGE

Optional a comfort package consisting of massage program and a lordosis support can be integrated against extra charge (see price sheet).

It can be chosen between an undulating massage program and a lordosis support via control panel (standing in front on the right). During the massage process the lordosis function can not be activated.

The massage process takes 10 minutes. The following reset time is ending after approx. 5 minutes. Then the program can be switched on again.

Only for armchairs with mains current (**rechargeable battery is not possible**).

LEGS

– No. 1. Metal rotary plate stainless steel, lightly curved



– No. 2. Metal rotary plate stainless steel with upholstered core (partially covered), lightly curved against extra charge see price list



– No. 3. Wooden rotary plate beech natural and in stain colours walnut, wenge and black, lightly curved



– No. 4. Stellate leg optional metal nickel satined (stainless steel optics) or metal powder-coated structural black mat



– No. 5. Stellate leg aluminium shiny (polished)



All tethered relax versions (with mains current) are possessing a turn limiter. These avoid that the electric cable wraps around the frame. Rotatability of these armchairs is approx. 320°. Relax versions actuated by rechargeable battery are rotatable by total 360°.



Please also note our general details and sales information

Edition 22.08.2024

Errors and amendments excepted. Our General Terms and Conditions are effective.

NECK CUSHION

Neck cushion with counter weight optional available in 3 sizes / shapes:

– **YN** 42 x 32 cm



– **YN2** 52 x 25 cm



– **YN1** 43 x 25 cm



COVERING MATERIALS

This armchair is available in leather and fabric.


You may find the information concerning the specific properties of the covering materials on the sample labels.



INDICATIONS OF DIMENSIONS AND REQUIREMENTS

All the values given are approximate values: dimensions in centimetres, material requirements in metres, leather requirements in square metres.

SECTIONAL DIMENSIONS



ORDER CHECK LIST

Please pay attention to the following issues respectively to complete specifications when ordering:

- **article / extra charges**
- **covering material**
- **leg version**; with wooden rotary plate also **stain colour**, with stellate leg (no. 4) also **finish**



Errors and amendments excepted. Our General Terms and Conditions are effective.

SILENCIO INNOVATION Leg part and back adjustable for a comfortable relax position. Adjustment optional motor-driven or motor-driven with LIFT-up stand up assistance. The comfort package massage / lordosis support can be integrated optionally.

I ARMCHAIRS MOTOR-DRIVEN

I ARMCHAIRS MOTOR-DRIVEN WITH LIFT-UP



Armchair small S	Armchair medium M	Armchair large L
VS2 	VM2 	VL2
92	92	92

Armchair small S	Armchair medium M	Armchair large L
VS4 	VM4 	VL4
92	92	92

extra charge comfort package massage

W

FABRIC	Requirement	3,40	3,70	3,80	3,40	3,70	3,80
COM							
10							
13							
16							
20							
25							
30							
45							




LEATHER	Requirement	6,50	6,50	6,60	6,50	6,50	6,60
COM							
X							
A							
B							
C							
D							
E							
F							
G							
Extra charge for battery:							
Extra charge for rotary plate with upholstered core:							



Errors and amendments excepted. Our General Terms and Conditions are effective.

I ACCESSORIES

Neck cushion w. counter weight Neck cushion w. counter weight Neck cushion w. counter weight

YN 	YN2 	YN1 
D 32	D 25	D 25
42	52	43

W

Requirement	0,70	0,60	0,50
COM			
10			
13			
16			
20			
25			
30			
45			

FABRIC

Requirement	0,90	0,80	0,70
COM			
X			
A			
B			
C			
D			
E			
F			
G			

LEATHER